


Fluke tools for industrial technicians



Applications

- 1 Tanks**
Thermal imager and pressure calibrator.
- 2 Process Controls**
Thermal imager and mA clamp meter.
- 3 PLCs/Network**
ScopeMeter test tool and mA clamp meter.
- 4 Motors/Pumps**
Digital multimeter, insulation tester, thermal imager, clamp meter, infrared thermometer and power quality analyzer.
- 5 Drives/MCC/Large Loads**
Digital multimeter, ScopeMeter test tool, power quality analyzer and thermal imager.
- 6 Electrical Cabinets**
Digital multimeter, clamp meter, infrared thermometer, thermal imager and power quality analyzer.
- 7 Conveyors**
Thermal imager and distance meter.
- 8 Switchgear/Transformers**
Power quality analyzer and thermal imager.