

Temperature specifications

[illegible]

Temperature compatibility

Model number	80AK-A	80BK-A	All 80PK Probes	80PJ-1/ 80PJ-9	80PT-25	80TK	80T- 150UA	80PJ-EXT	80PK-EXT	80PT-EXT	80CK-M	80CJ-M	80PR-60
10/11/12/12B			*			•	•		*		*		
110/111/112			*			•	•		*		*		
114/115/116/117	116	116	◆						▲		▲		
20/70 Series			*			•	•		*		*		
27						•	•		*		*		
70/73 III			*			•	•		*		*		
175/177			*			•	•		*		*		
179	•	•	▲						▲		▲		
80 Series III/83V			*			•			*		*		
87/89 IV	•	•	▲						▲		▲		
87V	•	•	▲						▲		▲		
187/189	•	•	▲				•		▲		▲		80PK-8
287/289	•	•	▲				•		▲		▲		
45/8845/8846			*			•	•		*		*		
43B			*			•	•		*		*		
90 Series			*			•	•		*		*		
120 Series			*			•	•		*		*		
190 Series			*			•	•		*		*		
50S/50D			•	•				•	•		•	•	
51/52/53/54 II			•	•	•			•	•	•	•	•	
63/66/68													66/68
714			•	•	•			•	•	•	•	•	
715			*			•	•		*		*		
725/726			•	•	•			•	•	•	•	•	
741/743/744			•	•	•			•	•	•	•	•	
787/789			*			•	•		*		*		
902	•	•	•						•				
1587	•	•	▲						▲		▲		
1577	•		▲										
561			•										
574/576			•										

• Compatible; * Requires 80TK; ▲ Requires 80AK-A; ◆116 only: requires 80AK-A